

Alternative Drive Controls Script



Customer Details

Client						
Assessor						
Organisation						
	ACC		DSS		Other	

Alternative Drive Controls

For assistance with Specialty Controls, please get in touch with your Technical Product Specialist. If you are unsure of who this is, please call us on 0800 31 61 81, to be directed to the right person.

Stealth i-Drive Head Array with Bluetooth (requires EDU or SCIM)



Optional Accessories:



Specs Switch
AB100-SPBK



Egg Switch

- ☐ **Black** ASL320BK
- ☐ **Green** ASL320GR*
- ☐ **Red** ASL320RD
- ☐ **Yellow** ASL320YL*



Egg Switch Mount
SPESM



Egg Switch Extension Cable
PRIDEELE155901



9" Lateral Rod with Ring*
SPSU260



13" Lateral Rod with Ring
SPSU264



18" Lateral Rod with Ring*
SPSU265



SCIM
.SCSCIMQL3



Figure 8
SPF8675-RING



Headrest Mount
Flip Down Compatible with Recline
SPUHB2D232FD




EDU (includes Gooseneck Mount)
.PKEDUQL3
PRIDEFRMASMB16062



Figure 8 & 13" Rod
SPF8675-RING
SPSU264
SPESM



Standard Stem Headrest Mount
SPUHB4D33200



Short Stem Headrest Mount
SPUHB2D33200

Stealth i-Drive Tri-Array Head Support with Bluetooth (requires EDU or SCIM)



Full Tri-Array
SPIDHBT200-U



Optional Accessories:



Specs Switch
AB100-SPBK



Egg Switch

- ☐ **Black** ASL320BK
- ☐ **Green** ASL320GR*
- ☐ **Red** ASL320RD
- ☐ **Yellow** ASL320YL*



Egg Switch Mount
SPESM



Egg Switch Extension Cable
PRIDEELE155901



SCIM
.SCSCIMQL3



Headrest Mount
Flip Down Compatible with Recline
SPUHB2D232FD



EDU (includes Gooseneck Mount)
.PKEDUQL3
PRIDEFRMASMB16062



Low Profile Facial Swing Away Receiver 2-PT*
SPSAR2B-B



Standard Stem Headrest Mount
SPUHB4D33200



Short Stem Headrest Mount
SPUHB2D33200

Stealth i Drive Pro Series Sip & Puff Head Array



Full Sip & Puff Head Array*
SPIDHBT310-U



Required:
Mounting
PRIDEMEC162072 and PRIDEMEC156032
Other
SPSAR2B-B Low Profile Facial Swing Away Receiver 2-PT
SP625M Straw*

Optional Accessories:



Specs Switch
AB100-SPBK



Egg Switch

☐ **Black** ASL320BK
☐ **Green** ASL320GR*
☐ **Red** ASL320RD
☐ **Yellow** ASL320YL*



Egg Switch Mount
SPESM



Egg Switch Extension Cable
PRIDEELE155901



Replacement Straw
SP625-S



Replacement Filter
SP625-F



Headrest Mount
Flip Down Compatible with Recline
SPUHB2D232FD



EDU (includes Gooseneck Mount)
.PKEDUQL3
PRIDEFRMASMB16062



Figure 8 & 13" Rod
SPF8675-RING
SPSU264
SPESM



Standard Stem Headrest Mount
SPUHB4D33200



Short Stem Headrest Mount
SPUHB2D33200

Switch Driving



Full Switch Driving* .SCSWITCH



Optional Accessories:



Specs Switch
AB100-SPBK



Buddy Button Black
DYNswTA5700



Buddy Button Red
DYNswTA5710



Buddy Button Green
DYNswTA5720



Buddy Button Yellow
DYNswTA5750



5 Way Splitter
DYNGSM9976



SCIM
PRIDECTL143988



Attendant Control
PRIDECTL143981
PRIDEWDR1010D298
PRIDEFRMASMB10455
PRIDEFRMASMB17115



**EDU (includes
Gooseneck Mount)**
.PKEDUQL3
PRIDEFRMASMB16062



Tray*
TRAYPRIDExxxxDIx



Full Switch Driving Pack

Includes (as pictured above):
5x Buddy buttons
5 way splitter
Tray
EDU

Chin Control



mo-Vis Chin Control Harness
SPM013-61

Required:

Mounting

SPM004-40-Q2M D6 Multi Adjustable Joint

SPM004-51-Q2M Multi JS Chin Control Adapter Set

SPM004-52 All-round JS Chin Control Adapter Set




Optional Accessories:



Micro Joystick*
SPIDM-MICRO-9



Headrest Mount
Flip Down Compatible with Recline
SPUHB2D232FD



Twister Switches (Flexi)*
SPIDCH-A1L
SPIDCH-A2R



EDU (includes Gooseneck Mount)
.PKEDUQL3
PRIDEFRMASMB1606



Standard Stem Headrest Mount
SPUHB4D33200



Short Stem Headrest Mount
SPUHB2D33200




Metric Headpad
SPACP150M



Tray Mounted Control Options

Chair width required _____"

Mount type required



Drop In



Slide On



Bayonet

Control required _____

Optional Accessories:



EDU (includes Gooseneck Mount)
.PKEDUQL3
PRIDEFRMASMB16062



Q-Logic 3 Multiplier Box Kit
.PKMULTIQL3

Note: For trial a wooden blank tray will be provided which can be drilled to allow for correct position of controller for trial.

Joystick Controller Options

☐ Stand Alone Joystick Pack



Codes Required:
PRIDECTL143980
ST-TWBM480CJ-Q
.PKEDUQL3
PRIDEFRMASMB16062

☐ Mini Proportional Joystick Pack



Codes Required:
SPIDPMP-9
.PKEDUQL3
PRIDEFRMASMB16062

☐ Attendant Control Pack



Codes Required:
PRIDECTL143981
PRIDEDWR1010D298
PRIDEFRMASMB10455
PRIDEFRMASMB17115

Codes Required for Recline:

PRIDECTL143981
PRIDEDWR1010D298
PRIDEMEC122827

☐ Stand Alone Joystick

SPST-ARM250T-Q For Recline Arms*
SPARM250-S For Tube Arms

If required for swing away or drop down

iAccess Enhanced Controls

☐ Buttons



Codes Required:
PRIDECTL144009
PRIDEMEC136981 for TB3 Arms-Mount
.PKMULTIQL3

☐ Toggle



Codes Required:
PRIDECTL144010
PRIDEMEC136981 for TB3 Arms-Mount
.PKMULTIQL3

☐ Bracket for Round Tube Arms PRIDEMEC19065

iAccess Enhanced Controls



The Q-Logic 3 enhanced display unit features a full colour LCD display, an industry standard D-9 connector to suit the integration with any aftermarket joystick or specialty control device, two 3.5 mm jack plugs allowing the fitment of auxiliary switches.

Connectivity is fully catered for with the Q-Logic 3 Enhanced Display Unit.

Bluetooth access to computer, tablet and phone functions including iOS and Android
Infrared remote control to access devices such as TV, Stereo, Sky TV, home automation

Bib Mounted Chin Control (requires EDU or SCIM)

☐ SPIDCH-M*



Stealth iDrive Control Harness Medium

This is a chin control harness and requires a mini proportional joystick.



An orbital compression mount and Stealth's proven highly adjustable, link style hardware, along with the addition of the track system allows for unmatched targeted positioning. This will implement the most optimal driving experience for the user.



With infinite positioning possibilities as well as a variety of switch mounting options that will attach to the collar, the Stealth i Drive Control Harness is the RIGHT choice for any lip, cheek, or chin driver!



The quick release, swing away, padded collar allows for the ability to remove the device from the right or the left side. The removable collar design also allows height adjustability on the collar frame independent of the adjustable link hardware.



The double padded collar consists of Closed Cell and SunMate foams. SunMate foam was originally designed for the NASA space program and provides a gentle touch for extended periods of time.

☐ SPIDPMP-9-FT

Stealth Mini Proportional Joystick



Twister Switches (Flexi)*

SPIDCH-A1L
SPIDCH-A2R

Stealth iDrive Control Harness Medium

This is a chin control harness and requires a mini proportional joystick.

Alternative Joysticks



Includes QL3EX Hand Control w/ Lighter Spring

Includes:
PRIDEKIT1902931
PRIDEDGN124307
PRIDECTL143976

☐ Lighter spring 120gm joystick force instead of std 240gm

mo-Vis All Round Lite Joystick



Stealth mo-Vis All Round Joystick Lite
SPIDM-ARLITE-9
Lighter spring 120gm joystick force instead of std 240gm



Stealth mo-Vis Satellite Twister Red
SPIDM-17*
Switches for use with SPIDM-ARLITE-9



Stealth mo-Vis Satellite Twister Blue
SPIDM-20*
Switches for use with SPIDM-ARLITE-9




Image of the Stealth mo-Vis All Round Joystick Lite with Satellite Switches

mo-Vis Heavy Duty Joystick



Stealth mo-Vis Heavy Duty Joystick
SPIDM-HD*
Requires an enhanced display or SCIM to function

If mounting on a gatlin mount, use SPIDM-HDMT*

mo-Vis Heavy Duty Joystick




Stealth Mini Proportional Joystick
SPIDPMP-9-FT
Requires an enhanced display or SCIM to function



Stealth IDPMP Topper Kit*
SPIDPMPJ-TOP
Requires an EDU or SCIM to function

Quantum Q-Logic 3e Hand Control (Does not require EDU or SCIM)

Q-Logic 3e Hand Control



Features:

- Works with Q-logic 3 system
- Operates up to 5 actuator functions
- Simple LCD display (icon based / Min text)
- Bluetooth and cable programming
- Interactive Assist capability
- Left and Right side charger option
- USB-C charger port
- Light functions operate off soft keys
- Programmable soft keys to offer I-access type functionality
- Day / Night screen via Page button long press

Power Modules:

- 120 Amp Q-logic 3

Magnetic Charger:

- Q-Logic 3e Magnetic Charger Lead
- PRIDEELE2103635

Stealth Alternate Joysticks – Force Required

Part Number	Joystick	Grams of Force	Newtons
SPIDM-MICRO-9*	Micro Joystick	≈8.5gf (0.02lbf)	≈8gf (0.08N)
SPIDPMP-9-FT	Precision Mini Proportional Joystick	43gf (0.09lbf)	43gf (0.42N)
SPIDM-MULTI-9*	Multi Joystick	49.89gf (0.11lbf)	49.89gf (0.49N)
SPIDM-ARLITE-9	All-Round Joystick Lite	120gf (0.26lbf)	120gf (1.18N)
SPMJM260Q*	Stealth Mushroom Joystick	227gf (0.50lbf)	227gf (2.23N)
SPIDM-ALLROUND-9*	All-Round Joystick	250gf (0.55lbf)	250gf (2.45N)
SPIDM-HD*	All-Round HD Joystick	650gf (1.43lbf)	650gf (6.38N)

mo-Vis Foot Control

☐ mo-Vis Foot Control Omni
SPP021-51

